

## Rooftop Support Systems

a division of Eberl Iron Works, Inc.  
128 Sycamore Steet  
Buffalo, New York 14204

(888) 243-2669  
RTS@eberliron.com  
rooftopsupportsystems.com



# RTSRAMP-5

## PRODUCT SUBMITTAL SHEET

### CROSSOVER RAMP

### Description

Crossover ramp units utilizing 12 gauge framing, anti-slip grating, and non-penetrating recycled rubber bases to provide safe pathways over rooftop obstacles for maintenance traffic.

### Product Information

**Compatible Bases:** RTSF21

**Clearance:** 16-5/8 in from top of roof

**Maximum Load Weight:** 36 in width - 460 lbs, 42 in width - 400 lbs, 48 in width - 350 lbs

**Framing:** Welded and single 1-5/8 in x 1-5/8 in, 12 gauge strut channel

**Grating:** 11-3/4 in and 9-1/2 in wide x 1-1/2 in high, 12 gauge anti-slip plank grating with 10 gauge carrier angles

**Framing/Grating Finish:** Pre-Galvanized (G90) or Hot Dip Galvanized (ASTM 123)

**Hardware Finish:** Electro-Galvanized (ASTM B633) or Hot Dip Galvanized (ASTM 123)



### Installation

1. Place bases on roof per design layout
2. Insert 1-5/8 in x 1-5/8 in strut uprights into square tube receiver on bases. Secure each with (1) 3/8 in channel nut and bolt (19 ft/lbs). All other framing hardware is 1/2 in tightened to 50ft/lbs
3. Attach grating to the platform sides (1-5/8 in x 3-1/4 in welded channel without bevel) to the grating with 1/2 in hardware
4. Attach to tops of 1-5/8 in strut uprights with 90 degree fitting and 1/2 in hardware
5. Repeat the process of attaching grating for the two ramp assemblies. This framing has 15 degree bevels on one end
6. Attach ramp assembly to platform using 15 degree fitting and 1/2 in hardware
7. Attach framing to base beneath ramps
8. Place transition piece at the end of each ramp

Quantity:

Contractor:

Project: